

FPX-AF-24APL08SR3

FPX Fiber Optic Adapter Pack with 3m Ribbon Pigtail, Singlemode, 24 fiber, LC adapter, left, blue, putty white

Product Classification

Regional Availability	North America
Product Type	Fiber adapter pack with pigtails
Product Series	FPX

General Specifications

Application	For use with FPX panels
Adapter Color	Blue
Adapters, quantity, front	12
Body Style	Duplex Left orientation
Color, front	Putty white
Interface	LC/UPC
Pigtail Assembly Type	Color-coded, 900 μ m Pigtail bundle
Pigtails Included, quantity	24
Total Fibers, quantity	24
Total Ports, quantity, front	24

Dimensions

Height	33.02 mm 1.3 in
Width	176.53 mm 6.95 in
Pigtail Length	3 m 9.843 ft

Ordering Tree

FPX-AF-24APL08SR3

FPX - AF - X X A P X X X X X X

Number of Fiber Ports per Bulkhead

12	12 Fibers ¹
24	24 Fibers ²
00	None

Pack Orientation

L	Left adapter pack
R	Right adapter pack

Adapter Style

00	None
Singlemode	
07	SC/APC
0J	SC/APC
08	LC/APC
0Z	LC/APC
Multimode	
A6	LCMM - AQUA ³
A9	SCMM - AQUA ³

Pigtail Length

LEAVE BLANK	Adapters only
3	3 meter pigtails

Pigtail Type

LEAVE BLANK	Adapters only
R	Ribbon
P	Stranded

Fiber Type

LEAVE BLANK	Adapters only
S	Singlemode
D	50/125 Multimode (OM3)
Q	50/125 Multimode (OM4)

¹ SC only

² LC only

³ CommScope recommends the use of aqua adapters to identify OM3 and OM4 circuits

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	OS2
Insertion Loss, maximum	0.3 dB
Return Loss, minimum	55 dB

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Storage Temperature	-40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights

Packaging quantity	1
Packaging Type	Bag Carton

Regulatory Compliance/Certifications

Agency	Classification
---------------	-----------------------

FPX-AF-24APL08SR3

CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

