


# FVM-19X175W

---



FVM Fiber Panel, unloaded, 1RU, 19 in, putty white

## Product Classification

<b>Regional Availability</b>	Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch panel
<b>Product Series</b>	FVM

## General Specifications

<b>Functionality</b>	Multiplexing   Patching   Splitting
<b>Application</b>	Standard 19"/23" rack mount
<b>Body Style</b>	Symmetrical
<b>Color</b>	Putty white
<b>Growth Configuration</b>	Unloaded
<b>Interface, front</b>	Unloaded
<b>Patch Cord Entry Location</b>	Front, left side   Front, right side
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	1
<b>Shelf Movement</b>	Fixed
<b>Total Ports, quantity</b>	0

## Dimensions

<b>Height</b>	44.45 mm   1.75 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	304.8 mm   12 in

## Material Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Steel

# FVM-19X175W

---

## Environmental Specifications

**Operating Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

### Agency

### Classification

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

