

FVM-LGX19X175-W

FVM, LGX compatible Fiber Panel, unloaded, 1RU, 19 in, putty white

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel
Product Series	FVM LGX

General Specifications

Functionality	Patching
Application	Used in LSX-style frames only
Body Style	Symmetrical
Color	Putty white
Growth Configuration	Unloaded
Interface, front	Unloaded
Module/Adapter Pack Slots, quantity	2
Rack Type	EIA 19 in EIA 23 in
Rack Units	1
Shelf Movement	Fixed
Total Ports, quantity	0

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in
Depth	279.4 mm 11 in

Material Specifications

Finish	Powder coated
Material Type	Steel

Packaging and Weights

Packaging quantity	1
---------------------------	---

FVM-LGX19X175-W

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

