

QBCB-HR

Q3000 Blank Blade Cover for unused panel slots

Product Classification

Regional Availability Australia/New Zealand | EMEA | Latin America | North America

Product Type Cover

Dimensions

Height 19.05 mm | 0.75 in

Width 373.126 mm | 14.69 in

Depth 39.624 mm | 1.56 in

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Relative Humidity 5%–95%, non-condensing

Environmental Space Indoor

Flammability Rating UL 94 V-0

Packaging and Weights

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

