TFP-24APLQ5

TFP Fiber Optic Adapter Pack, Singlemode, 6 quad LC UPC adapters, left, blue

Product Classification

Regional Availability Asia | Latin America | North America

Portfolio NETCONNECT®

Product Type Fiber adapter pack

Product Series TFP

General Specifications

Application For use with TFP panels

Adapter Color Blue

Adapters, quantity, front 6

Body Style Left orientation | Quad

Color, frontBlackInterfaceLC/UPC

Total Ports, quantity, front 24

Dimensions


 Height
 33.53 mm | 1.32 in

 Width
 176.02 mm | 6.93 in

Ordering Tree



TFP-24APLQ5



Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Operating Temperature $0 \, ^{\circ}\text{C to} + 70 \, ^{\circ}\text{C (+32 °F to} + 158 °F)$ **Storage Temperature** $-40 \, ^{\circ}\text{C to} + 70 \, ^{\circ}\text{C (-40 °F to} + 158 °F)$

Packaging and Weights

Packaging quantity

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



TFP-24APLQ5



