

SSC-760236966E1 | 12 in Pole Top for Ericsson



Top of Pole 12in Dia Concealment Enclosure for up to four Ericsson 220x/440x/4435 radios and Power Distribution or Diplexer

- Enclosure for holding up to 4 metro cell radios directly below a multiband canister antenna
- Orderable to mount multi-band and multi-port antennas from multiple antenna vendors
- Variable pole diameter mounting kits available to mount to existing structures
- Matching light pole or monopole options available

Pole Top Concealment that can accommodate most antenna manufacturers antennas. Please reach out to your CommScope Representative for exact model number.

Additional Configurations available utilizing the below kits:

-860664822-AMK-001 PTS power distribution (replaces Raycap)

-860664822-AMK-002 (1) 4435 radio,raycap,(2) 220x/440x radios

-Supports "V4S4SSP-360S-F2" and "NNV4SSP-360S-F2" antenna with separately ordered "860664552" bracket

Mounts directly to CommScope poles with no additional mounting materials. Mounts to other wood and metal poles with separately purchased mounts.

Product Classification

Portfolio	CommScope®
Product Type	Pole top
Product Brand	Metro Cell
Ordering Note	CommScope® standard product with terms
Warranty	One year

General Specifications

Antenna Compatibility, CommScope	CommScope Canister Antennas
Antenna Compatibility, Other Vendors	ACE AMPHENOL DK GALTRONICS GAMMA NU JMA KATHREIN KMW ROSENBERGER
Antennas Included	None
Color Options	Antique Bronze (SRSL 45893) Beige-Grey (RAL 7006) Black (RAL 9005) Black Green (RAL 6012) Brown (RAL 8014) Fairfax Brown (SW 2856) Faux Concrete Federal Park Brown Green (RAL 6005) Light Gray (RAL 7035) Metallic Silver Signal Black (RAL 9004) White (RAL 9010)
Cooling	Passive Cooling
Mounting Options	Non-tapered poles Tapered poles Wood poles
Radio Compatibility, Ericsson	220x 440x 4435 Diplexer Power Distribution

SSC-760236966E1 | 12 in Pole Top for Ericsson

Radios Included	None
Dimensions	
Height	914.4 mm 36 in
Width	304.8 mm 12 in
Depth	304.8 mm 12 in
Mounting Bolt Circle Diameter	142.748 mm 5.62 in 241.3 mm 9.5 in

Material Specifications

Finish Aluminum	Chromate
Finish Concealment Covers	Powder coated
Material Type	Aluminum Steel

Environmental Specifications

Thermal Compliance	GR-487
---------------------------	--------

Packaging and Weights

Volume	0.067 m ³ 2.36 ft ³
Weight (unloaded)	26.308 kg 58 lb

* Footnotes

Warranty	For more information, please consult our Product Warranty guidelines
-----------------	--