

# SSC-760237600



## Middle of Pole Micro Concealment Enclosure for up Low, Mid, and High Power Samsung, Ericsson, and Nokia Radios

- Intended to be used with high powered remote radio heads on standard street lighting and wood pole structures where low-visual impact is desired
- Enables attractive concealment and securing of all site equipment on standard street lighting structures
- Highly-flexible configuration can house diplexers, AC load center, and/or fiber demarcation

SSC-760237600E1x Ericsson  
SSC-760237600E2x Ericsson 4490/4890  
SSC-760237600S1x Samsung  
SSC-760237600N3x Nokia

Includes Standard Mounting kit for through bolt, clamp, and banding

Available After Market KIts, ordered separate:

-860649584S-xx 5" Standoff for wood poles  
-860649584ST-xx Standoff for Round Tapered Poles  
-860661938-S1 Nokia to Samsung Retrofit Kit

## Product Classification

<b>Product Type</b>	Mid pole
<b>Product Brand</b>	Metro Cell
<b>Ordering Note</b>	ANDREW® standard product with terms
<b>Warranty</b>	One year

## General Specifications

<b>Antennas Included</b>	None
<b>Color</b>	Light Gray (RAL 7035)
<b>Color Options</b>	Beige-Grey (RAL 7006)   Black (RAL 9005)   Black Green (RAL 6012)   Brown (RAL 8014)   Faux Concrete   Green (RAL 6005)   Metallic Silver   Umbra Grey (RAL 7022)   White (RAL 9010)
<b>Cooling</b>	Passive Cooling
<b>Mounting Options</b>	Non-tapered poles   Tapered poles   Wood poles
<b>Power Supply Compatibility</b>	CCI PSU-1200W-48-N   DELTA 1.0   DELTA 2.0   PSU-AC-08
<b>Radio Compatibility, Ericsson</b>	220x   440x   4415   4426   4435   4449   4455   4490   4890   8843   Diplexer   PSU-AC-08   Power Distribution
<b>Radio Compatibility, Nokia</b>	AHBCA   AHFIA   AHFIB   AHFIC   AHLBA   CCI   Diplexer   Power Distribution
<b>Radio Compatibility Samsung</b>	Diplexer   Power Distribution   RF4402D-D1A   RFV01U-D1A   RT2201-46A   RT4401-48A

# SSC-760237600

---

**Radios Included**                      None

## Dimensions

**Height**                                      1,117.6 mm | 44 in

**Width**                                        533.4 mm | 21 in

**Depth**                                        508 mm | 20 in

## Electrical Specifications

**Power/Fiber Input**                      Trade size knockouts at rear side

## Material Specifications

**Finish Aluminum**                        Chromate

**Finish Concealment Covers**           Powder coated

**Material Type**                              Aluminum | Steel

## Environmental Specifications

**Thermal Compliance**                    GR-487

## Packaging and Weights

**Volume**                                      0.303 m<sup>3</sup> | 10.7 ft<sup>3</sup>

**Weight (loaded)**                            136.078 kg | 300 lb

**Weight (unloaded)**                        49.895 kg | 110 lb