



Fiber Optic Patch Cord, Duplex, Multimode, LC/UPC to LC/UPC, Aqua

Product Classification

| | |
|------------------------------|--|
| Regional Availability | Asia Australia/New Zealand China India |
| Portfolio | CommScope® |
| Product Type | Fiber patch cord, duplex |

General Specifications

| | |
|-------------------------------|----------------|
| Color, boot A | Aqua |
| Color, boot B | Aqua |
| Color, connector A | Beige |
| Color, connector B | Beige |
| Connector A, quantity | 2 |
| Connector B, quantity | 2 |
| Interface, Connector A | LC/UPC |
| Interface, Connector B | LC/UPC |
| Jacket Color | Aqua |
| Polarity | Pairs, flipped |
| Total Fibers, quantity | 2 |

Material Specifications

| | |
|------------------------|-------------------------------|
| Jacket Material | Low Smoke Zero Halogen (LSZH) |
|------------------------|-------------------------------|

Mechanical Specifications

| | |
|--|----------------|
| Cable Retention Strength, maximum | 11.24 lb @ 0 ° |
|--|----------------|

Optical Specifications

| | |
|-------------------|-----------|
| Fiber Mode | Multimode |
|-------------------|-----------|

1920743

| | |
|--------------------------------|---------|
| Fiber Type | OM3 |
| Insertion Loss, maximum | 0.15 dB |
| Return Loss, minimum | 35 dB |

Environmental Specifications

| | |
|--------------------------------|---|
| Operating Temperature | -10 °C to +60 °C (+14 °F to +140 °F) |
| Qualification Standards | IEC 60332-1 IEC 60332-3 IEC 60754 IEC 61034 |

Packaging and Weights

| | |
|---------------------------|---|
| Packaging quantity | 1 |
|---------------------------|---|

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |

