


# C240-NRQMR

Base Product



CNT-240 CNT® Jumper with interface types N Male Right Angle and QMA Male Right Angle, variable length

## Product Classification

|                |                        |
|----------------|------------------------|
| Product Type   | Braided cable assembly |
| Product Brand  | CNT®                   |
| Product Series | CNT-240                |

## General Specifications

|                                    |                                                                                                               |
|------------------------------------|---------------------------------------------------------------------------------------------------------------|
| Body Style, Connector A            | Right angle                                                                                                   |
| Body Style, Connector B            | Right angle                                                                                                   |
| Cable Family                       | CNT-240                                                                                                       |
| Interface, Connector A             | N Male                                                                                                        |
| Interface, Connector B             | QMA Male                                                                                                      |
| Orientation                        | 0°                                                                                                            |
| Specification Sheet Revision Level | A                                                                                                             |
| Variable Length                    | For custom lengths contact 828-324-2200 or 1-800-982-1708 (toll free), or your local CommScope representative |

## Dimensions

|              |            |
|--------------|------------|
| Length       | 0 m   0 ft |
| Nominal Size | 0.240 in   |

## VSWR/Return Loss

| Frequency Band | VSWR  | Return Loss (dB) |
|----------------|-------|------------------|
| 700–3000 MHz   | 1.433 | 14.99            |

## Jumper Assembly Sample Label

# C240-NRQMR



## Regulatory Compliance/Certifications

| Agency        | Classification                                                                 |
|---------------|--------------------------------------------------------------------------------|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

## Included Products

|              |                                                                                 |
|--------------|---------------------------------------------------------------------------------|
| 240BPNR-CR   | - Type N Male Right Angle for CNT-240 and CNT-240-Flex braided cable            |
| 240PQMR-C-CR | - QMA Male Right Angle for CNT-240 braided cable                                |
| 240PQMR-CA   | - QMA Male Right Angle for CNT-240 braided cable, for jumpers only not for sale |
| CNT-240      | - CNT-240, CNT® 50 Ohm Braided Coaxial Cable, black PE jacket                   |
| CNT-240-SFR  | - CNT-240-SFR, CNT® 50 Ohm Braided Coaxial Cable, black PE jacket               |