C300-NMNM

Base Product



Product Classification

Product Type Braided cable assembly

Product Brand CNT®
Product Series CNT-300

General Specifications

Attachment, Connector A Factory attached

Attachment, Connector B Factory attached

Body Style, Connector A Straight
Body Style, Connector B Straight
Cable Family CNT-300
Interface, Connector A N Male
Interface, Connector B N Male

Specification Sheet Revision Level

Variable Length For custom lengths, contact your local ANDREW representative

Dimensions

 Length
 0 m | 0 ft

 Nominal Size
 0.300 in

VSWR/Return Loss

Frequency Band VSWR Return Loss (dB)

700–3000 MHz 1.433 14.99

Jumper Assembly Sample Label





Regulatory Compliance/Certifications

Classification Agency

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Included Products

Type N Male for CNT-300 braided cable 300APNM-C

CNT-300, CNT® 50 Ohm Braided Coaxial Cable, black PE jacket CNT-300

CNT-300-SFR, CNT® 50 Ohm Braided Coaxial Cable, black non-halogenated, fire retardant CNT-300-SFR

polyolefin jacket, Class B2ca, -s1a, d1, a1

CNT-300, CNT® 50 Ohm Braided Coaxial Cable, black PE jacket CNT-300A

CNT-300, CNT® 50 Ohm Low Braided Coverage Coaxial Cable, black non-halogenated jacket CNT-300A-LB CNT-300A-SFR, CNT® 50 Ohm Braided Coaxial Cable, black non-halogenated, fire retardant CNT-300A-SFR

polyolefin jacket, Class B2ca, -s1a, d1, a1

