C400-TMTM

Base Product



CNT-400 CNT® Jumper with interface types TNC Male and TNC Male variable length

Product Classification

Product Type Braided cable assembly

Product Brand CNT®
Product Series CNT-400

General Specifications

Body Style, Connector A Straight
Body Style, Connector B Straight
Cable Family CNT-400
Interface, Connector A TNC Male
Interface, Connector B TNC Male

Specification Sheet Revision Level A

Variable Length For custom lengths, contact your local ANDREW representative

Dimensions

 Length
 0 m | 0 ft

 Nominal Size
 0.400 in

VSWR/Return Loss

Frequency Band VSWR Return Loss (dB)

700–3000 MHz 1.433 14.99

Jumper Assembly Sample Label





Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Included Products

400BPTM-C - TNC Male for CNT-400 braided cable 400BPTM-C-CR - TNC Male for CNT-400 braided cable 400PTM-C - TNC Male for CNT-400 braided cable