

# C400D-TMBNF

Base Product



CNT-400-DB CNT® Jumper with interface types TNC Male and N Female Bulkhead, variable length

## Product Classification

Product Type	Braided cable assembly
Product Brand	CNT®
Product Series	CNT-400

## General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Bulkhead
Cable Family	CNT-400
Interface, Connector A	TNC Male
Interface, Connector B	N Female
Specification Sheet Revision Level	A
Variable Length	For custom lengths, contact your local ANDREW representative

## Dimensions

Length	0 m   0 ft
Nominal Size	0.400 in

## Electrical Specifications

3rd Order IMD	-115 dBm
3rd Order IMD Test Method	Two +43 dBm carriers

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.135	23.98

## Jumper Assembly Sample Label

# C400D-TMBNF



## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

## Included Products

400BPTM-C	- TNC Male for CNT-400 braided cable
400BPTM-C-CR	- TNC Male for CNT-400 braided cable
400PNF-BHC	- Type N Female Bulkhead for CNT-400 braided cable
400PTM-C	- TNC Male for CNT-400 braided cable
CNT-400-DB	- CNT-400-DB, CNT® 50 Ohm Braided Coaxial Cable, flooded, black PE jacket