

# F1A-HMHM-AT

Base Product



FSJ1-50A SureFlex® Jumper with interface types 4.3-10 Male and 4.3-10 Male, AT&T

- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

## Product Classification

Product Type	Wireless transmission cable assembly
Product Brand	HELIAX®   SureFlex®
Product Series	FSJ1-50A

## General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	4.3-10 Male
Interface, Connector B	4.3-10 Male
Specification Sheet Revision Level	A

## Dimensions

Length	1 m   3.281 ft
Nominal Size	1/4 in

## Electrical Specifications

3rd Order IMD	-118 dBm
3rd Order IMD Test Method	Two +43 dBm carriers

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.196	20.99
1700–2700 MHz	1.196	20.99

## Jumper Assembly Sample Label

# F1A-HMHM-AT



## Environmental Specifications

**Immersion Test Method** Meets IEC 60529:2001, IP68 in mated condition

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system