# F1A-PNMDM

#### **Base Product**

FSJ1-50A SureFlex® Jumper with interface types N Male and 7-16 DIN Male, variable length

## Product Classification

Product Type		Wireless transmission cable assembly
Product Brand		HELIAX®   SureFlex®
Product Series		FSJ1-50A
General Specifications		
Body Style, Connector A		Straight
Body Style, Connector B		Straight
Interface, Connector A		N Male
Interface, Connector B		7-16 DIN Male
Specification Sheet Revision Level		A
Variable Length		For custom lengths, contact your local ANDREW representative
Dimensions		
Length		0 m   0 ft
Nominal Size		1/4 in
VSWR/Return Loss		
Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.43	15.04

# Jumper Assembly Sample Label



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 18, 2025

Page 1 of 2

# F1A-PNMDM



## **Environmental Specifications**

**Immersion Test Method** 

Meets IEC 60529:2001, IP68 in mated condition

### Regulatory Compliance/Certifications

#### Agency

ISO 9001:2015

### Classification

Designed, manufactured and/or distributed under this quality management system



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 18, 2025

Page 2 of 2