# F1R-DMDR-P

#### **Base Product**

FSJ1RK-50B SureFlex® Jumper with interface types 7/16 Din Male and 7 16 Din Male Right Angle, variable length

## Product Classification

Product Type		Wireless transmission cable assembly
Product Brand		HELIAX®   SureFlex®
Product Series		FSJ1-50B
General Specifications		
Body Style, Connector A		Straight
Body Style, Connector B		Right angle
Interface, Connector A		7-16 DIN Male
Interface, Connector B		7-16 DIN Male
Specification Sheet Revision Level		A
Variable Length		For custom lengths, contact your local ANDREW representative
Dimensions		
Length		0 m   0 ft
Nominal Size		1/4 in
Electrical Specifications		
3rd Order IMD Static		-107 dBm
3rd Order IMD Static Test Method		Two +43 dBm carriers
VSWR/Return Loss		
Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.152	23.02
1700–2200 MHz	1.152	23.02
2200–2700 MHz	1.152	23.02

# Jumper Assembly Sample Label

ANDREW an Amphenol company

Page 1 of 2

©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 18, 2025

# F1R-DMDR-P



## **Environmental Specifications**

EN50575 CPR Cable EuroClass Fire Performance	B2ca
EN50575 CPR Cable EuroClass Smoke Rating	s1a
EN50575 CPR Cable EuroClass Droplets Rating	d0
EN50575 CPR Cable EuroClass Acidity Rating	al
Immersion Test Method	Meets IEC 60529:2001, IP68 in mated condition

### Regulatory Compliance/Certifications

#### Classification

ISO 9001:2015

Agency

Designed, manufactured and/or distributed under this quality management system

