FJWMPMPDM

Base Product



Singlemode MPO (Unpinned) to MPO (Unpinned), InstaPATCH® 360 Pre-terminated Indoor/Outdoor Trunk Cable, 144-Fiber, Low Smoke Zero Halogen

Product Classification

Regional Availability Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

Product Type Fiber trunk cable assembly **Product Brand** SYSTIMAX InstaPATCH® 360

Ordering Note For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length

may vary based on cable configuration

General Specifications

Color, boot A Black Color, connector A Green Color, boot B Black Color, connector B Green

Construction Type InstaPATCH® 360 trunk/extension/cross-connect, indoor/outdoor

Furcation Color Yellow

Interface, Connector A MPO-12/APC Female Interface, Connector B MPO-12/APC Female

Jacket Color Black

Polarity Method B (LL)

Fibers per Subunit, quantity 12 Total Fibers, quantity 144


Dimensions

Cable Assembly Length Range (m) 3 - 999Cable Assembly Length Range (ft) 10 - 999



FJWMPMPDM

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.652.D | G.657.A1, TeraSPEED®

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Environmental Space Dual Rated LSZH/Riser | Indoor/Outdoor | Outdoor

COMMSCOPE®

FJWMPMPDM

Regulatory Compliance/Certifications

Classification **Agency**

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system **REACH-SVHC** Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant **UK-ROHS** Compliant



Included Products

Fiber Indoor/Outdoor cable, TeraSPEED® Low Smoke Zero Halogen Riser MPO Trunk, Gel-Free, 760150813 Z-144-MP-8W-F12BK/D

144 fiber multi-unit with 12 fiber subunits, Singlemode G.652.D and G.657.A1, Feet jacket

marking, Black jacket color, Dca flame rating

MPO12, LOW LOSS, FEMALE, Singlemode, GREEN, 3mm 860366137

