CBCCF | IP6A-18RUTP-02H-02H



InstaPATCH® Cu GigaSPEED X10D® U/UTP Riser Preterminated Copper Cable, dual row high density outlet to dual row high density outlet, 18 links

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Copper trunk cable assembly

Product Brand GigaSPEED X10D® | InstaPATCH® Cu

General Specifications

ANSI/TIA Category 6A

Cable Type U/UTP (unshielded)

Conductor Type Solid

Interface, Connector A Information outlet

Interface Feature, connector A Dual row | High density

Interface, Connector B Information outlet

Interface Feature, connector B Dual row | High density

Link Count 18

Wiring T568B

Dimensions

Cable Assembly Length Range (m) 5 – 90

Cable Assembly Length Range (ft) 17 – 295


Electrical Specifications

dc Resistance, maximum0.3 ohmSafety Voltage Rating300 V

Ordering Tree



CBCCF | IP6A-18RUTP-02H-02H



Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \text{ (+14 }^{\circ}\text{F to } +140 \,^{\circ}\text{F)}$

Environmental Space Riser

Flammability Rating UL 94 V-0

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Included Products

1091B-4/23 - GigaSPEED X10D® 1091B ETL Verified Category 6A U/UTP Cable, 4 pair

count

MGS600 - GigaSPEED X10D® M-Series Modular Jack, RJ45, Cat6A Unshielded

