## FBXLCUC11



#### OM4 LC to Unconnectorized, Fiber Pigtail, 0.9 mm SBJ

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

**Product Type** Fiber pigtail, unjacketed

Product Brand SYSTIMAX InstaPATCH® 360

Ordering Note Minimum length may vary based on cable configuration

#### General Specifications

Color, boot A Aqua

Color, connector A Black

Interface, Connector A LC/UPC

Jacket Color Aqua

Total Fibers, quantity


#### **Dimensions**

Cable Assembly Length, minimum (ft) 1
Cable Assembly Length, maximum (ft) 23
Cable Assembly Length, minimum (m) 1
Cable Assembly Length, maximum (m) 7

### Ordering Tree



## FBXLCUC11



#### Mechanical Specifications

Cable Retention Strength, maximum  $2.00 \text{ lb} @ 90 \degree | 5.00 \text{ lb} @ 0 \degree$ 

**Optical Specifications** 

**Fiber Mode** Multimode

**Fiber Type** OM4, LazrSPEED®

### **Environmental Specifications**

**Operating Temperature**  $-10 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \text{ (+14 }^{\circ}\text{F to } +140 \,^{\circ}\text{F)}$ 

**Environmental Space** Low Smoke Zero Halogen (LSZH)

Packaging and Weights

Packaging quantity 2

#### Regulatory Compliance/Certifications

# AgencyClassificationCHINA-ROHSBelow maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant



#### Included Products

760010603 – LazrSPEED® 0.9 mm Low Smoke Zero Halogen Reinforced Buffered Fiber

N-001-RF-5K-F09AQ Cable

860657284 – LC/PC Connector, Multimode, Aqua

Page 2 of 3



# FBXLCUC11

