

FSWL2UCWH

Base Product



TeraSPEED® LC/UPC Keyed Yellow to Unconnectorized, Distribution Cable, 48-Fiber, Plenum

Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	Fiber distribution cable assembly
Product Brand	SYSTIMAX InstaPATCH® 360
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters

General Specifications

Cable Glands	No glands
Color, connector A	Yellow
Construction Type	Distribution, indoor
Interface, Connector A	LC/UPC
Interface Feature, connector A	Keyed
Interface, Connector B	Unterminated
Total Fibers, quantity	48

Dimensions

Cable Assembly Length Range (m)	1 – 61
Cable Assembly Length Range (ft)	1 – 200

Mechanical Specifications

Cable Retention Strength, maximum	0.50 lb @ 0 ° 0.50 lb @ 90 °
--	--------------------------------

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.652.D G.657.A1, TeraSPEED®

FSWL2UCWH

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Indoor | Plenum

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

Included Products

- | | | |
|-----------------------------|---|--|
| 760102921
SFC-LCR-09-KYL | - | TeraSPEED® Behind The Wall Keyed LC Connector for 0.9 mm Fiber, Singlemode, yellow |
| P-048-DS-8W-FMU | - | Fiber indoor cable, TeraSPEED® Plenum Distribution, 48 fiber multi-unit with 12 fiber subunits, Singlemode G.652.D and G.657.A1, Gel-free, Feet jacket marking |