
U4GLGLGCL

Base Product



Ultra Low Loss ULL TeraSPEED® LC/APC G B to LC/APC G B Ruggedized fanout Cable, 96-Fiber, LSZH, 12 fiber PmP 2.0 mm /B2ca

Product Classification

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle

East/Africa | North America

Portfolio CommScope®

Product Type Ruggedized fanout

Product Brand SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales

Representative | For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may vary based on cable configuration

General Specifications

 Color, boot A
 Green

 Color, connector A
 Green

 Color, boot B
 Green

 Color, connector B
 Green

 Construction Type
 Stranded

 Furcation Color
 Yellow

Interface, Connector A LC/APC

Interface Feature, connector A Grade B performance

Interface, Connector B LC/APC

Interface Feature, connector B Grade B performance

Jacket ColorYellowFibers per Subunit, quantity12Total Fibers, quantity96

Dimensions

Cable Assembly Length Range (m) 3 – 999



U4GLGLGCL

Cable Assembly Length Range (ft) 8 – 999

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A2, TeraSPEED®

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (+14 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$

EN50575 CPR Cable EuroClass Fire Performance B2ca

Environmental Space Indoor | Low Smoke Zero Halogen (LSZH)

Regulatory Compliance/Certifications

Agency Classification
ANATEL Compliant

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant





