U4GLULUCH

Base Product



Ultra Low Loss ULL TeraSPEED® LC/UPC Uniboot to LC/UPC Uniboot Ruggedized fanout Cable, 48-Fiber, LSZH, 12 fiber PmP 2.0 mm /B2ca

Product Classification

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle

East/Africa | North America

Portfolio CommScope®

Product Type Ruggedized fanout

Product Brand SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales

Blue

Representative | For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may vary based on cable configuration

General Specifications

Color, boot A Blue

Color, connector A Green

Color, boot B Blue

Construction Type Stranded

Furcation Color Yellow

Interface, Connector A LC/UPC

Interface Feature, connector A Uniboot

Interface, Connector B LC/UPC

Interface Feature, connector B Uniboot

Jacket Color Yellow

Fibers per Subunit, quantity 12

Total Fibers, quantity 48

Dimensions

Color, connector B

Cable Assembly Length Range (m) 3 - 999

Cable Assembly Length Range (ft) 8 - 999

Page 1 of 2



U4GLULUCH

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A2, TeraSPEED®

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

EN50575 CPR Cable EuroClass Fire Performance B2ca

Environmental Space Indoor | Low Smoke Zero Halogen (LSZH)

Regulatory Compliance/Certifications

AgencyClassificationANATELCompliantCHINA-ROHSBelow maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



