## U4VMXLUCD

Base Product



Ultra Low Loss ULL LazrSPEED® 550 OM5 MPO(Pinned) to LC/UPC Uniboot Ruggedized fanout Cable, 12-Fiber, LSZH, 12 fiber PmP 2.0 mm /B2ca

in meters | Minimum length may vary based on cable configuration

#### Product Classification

Regional Availability	Europe   Middle East/Africa
Portfolio	CommScope®
Product Type	Ruggedized fanout
Product Brand	SYSTIMAX ULL
Ordering Note	For additional jacket colors, please contact a CommScope Sales Representative   For lengths greater than 999 ft (304 m), orders must be

#### General Specifications

Cable Assembly Length Range (ft)

Color, boot A	Lime green
Color, connector A	Gray
Color, boot B	Lime green
Color, connector B	Lime green
Construction Type	Stranded
Furcation Color	Lime green
Interface, Connector A	MPO-12/UPC Male
Interface, Connector B	LC/UPC
Interface Feature, connector B	Uniboot
Jacket Color	Lime green
Polarity	Method B Enhanced (ULL)
Fibers per Subunit, quantity	12
Total Fibers, quantity	12
Dimensions	
Cable Assembly Length Range (m)	2 - 304

Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 16, 2024

7 - 999



# U4VMXLUCD

## Ordering Tree

	BASE	CODE		Ŀ	÷
	Jacket Color		Breakout Length / Option	ι	.ength
N	Lime Green	А	33 in breakout, no gland		
		в	33 inch breakout, with gland on side A		
		С	33 inch breakout, pulling grip on side A		
		E	24 inch breakout, no gland		
		F	24 inch breakout, with gland on side A		NOM
		G	24 inch breakout, pulling grip on side A	F	Feet
		н	48 inch breakout, no gland	Μ	Meter
		J	48 inch breakout, with gland on side A		
		К	48 inch breakout, pulling grip on side A		
		L	72 inch breakout, no gland		
		М	72 inch breakout, with gland on side A		
		Ν	72 inch breakout, pulling grip on side A		
		S	36 inch breakout, no gland		
		т	36 inch breakout, pulling grip on side A		
		U	36 inch breakout, with gland on side A		
		V	60 inch breakout, no gland		
		w	60 inch breakout, no gland, with pulling grip on side A		
		2	60 inch breakout, with gland on side A		
		3	60 inch breakout, with gland and pulling grip on side A		
		4	23 inch breakout, mounting clips included, no pulling grip on side A		
		5	23 inch breakout, mounting clips included, pulling grip on side A		

### Optical Specifications

Fiber Mode

Fiber Type

Multimode OM5, LazrSPEED®

### Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)	
EN50575 CPR Cable EuroClass Fire Performance	B2ca	
Environmental Space	Indoor   Low Smoke Zero Halogen (LSZH)	

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 16, 2024



# U4VMXLUCD

### Regulatory Compliance/Certifications

#### Agency

#### Classification

CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 16, 2024

