


UDVLC42

Base Product



Ultra Low Loss OM5, LC/UPC to LC/UPC, Fiber Patch Cord, 1.6 mm Duplex, Plenum

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin America | Middle East/Africa | North America

Portfolio

CommScope®

Product Type

Fiber patch cord, duplex

Product Brand

SYSTIMAX ULL

Product Series

UDV

Ordering Note

For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may vary based on cable configuration

General Specifications

Color, boot A

Lime green

Color, connector A

Black

Color, boot B

Lime green

Color, connector B

Black

Interface, Connector A

LC/UPC

Interface, Connector B

LC/UPC

Jacket Color

Lime green

Polarity

Pairs, flipped

Total Fibers, quantity

2

Dimensions

Cable Assembly Length Range (m)

1 – 999

Cable Assembly Length Range (ft)


1 – 999

Diameter Over Jacket

1.6 mm | 0.063 in

Ordering Tree

UDVLC42



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode Multimode

Fiber Type OM5, LazrSPEED®

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Plenum

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
ANATEL	Compliant
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



Included Products

760233361 - Fiber indoor cable, LazrSPEED® 1.6 mm Plenum Zipcord, Multimode OM5, Feet jacket marking,

UDVLC42

P-002-ZC-5G-F16LM Lime green jacket color
860655463 - LC/PC Connector, Multimode, Lime