


UGGMPMXRP

Base Product



Ultra Low Loss (ULL) Singlemode MPO12 (Unpinned) to MPO12 (Pinned), Fiber Trunk Cable Assembly, 288-Fiber, Rollable Ribbon Central Tube, Plenum

Product Classification

| | |
|-----------------------|--|
| Regional Availability | Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber trunk cable assembly |
| Product Brand | SYSTIMAX ULL |
| Ordering Note | For additional jacket colors, please contact a CommScope Sales Representative For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration |

General Specifications

| | |
|------------------------------|-------------------------|
| Color, boot A | Black |
| Color, connector A | Green |
| Color, boot B | Black |
| Color, connector B | Green |
| Construction Type | Rollable ribbon |
| Furcation Color | Yellow |
| Interface, Connector A | MPO-12/APC Female |
| Interface, Connector B | MPO-12/APC Male |
| Jacket Color | Yellow |
| Polarity | Method B Enhanced (ULL) |
| Fibers per Subunit, quantity | 12 |
| Total Fibers, quantity | 288 |


Dimensions

| | |
|---------------------------------|---------|
| Cable Assembly Length Range (m) | 3 – 999 |
|---------------------------------|---------|

UGGMPMXRP

Cable Assembly Length Range (ft) 10 – 999

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A2, TeraSPEED®

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Plenum

Regulatory Compliance/Certifications

| | |
|---------------|--|
| Agency | Classification |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

Included Products

- | | | |
|--------------------------|---|--|
| 760239140 | – | Fiber indoor cable, Plenum All-Dielectric Central Tube Rollable Ribbon, 288 fiber, Singlemode G. |
| P-288-CN-RR-F12YL/8G/99E | | 657.A2, Feet jacket marking, Yellow jacket color |
| 860638317 | – | MP012, ULTRA LOW LOSS, MALE, Singlemode, GREEN, 3mm |
| 860638318 | – | MP012, ULTRA LOW LOSS, FEMALE, Singlemode, GREEN, 3mm |