## UGV2P2XBM

**Base Product** 



# Ultra Low Loss (ULL) OM5 MPO24 (Unpinned) to MPO24 (Pinned), Fiber Trunk Cable Assembly, 144-Fiber, Plenum

### Product Classification

Regional Availability	Asia   Australia/New Zealand   China   Europe   India   Latin America   Middle East/Africa   North America	
Portfolio	CommScope®	
Product Type	Fiber trunk cable assembly	
Product Brand	SYSTIMAX ULL	
Ordering Note	For additional jacket colors, please contact a CommScope Sales Representative   For lengths greater than 999 ft (304 m), orders must be in meters   Minimum length may vary based on cable configuration	
General Specifications		

Red
Lime green
Red
Lime green
Stranded
Lime green
MPO-24/UPC Female
MPO-24/UPC Male
Lime green
Method B Enhanced (ULL)
24
144
33 in
3 - 999
10 - 999

Page 1 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 20, 2025



## UGV2P2XBM

### Ordering Tree

	B	ASE C	ODE – N	$\left  \cdot \right $	
J	acket Color		Breakout Length / Option	L	ength
N	Lime green	А	33 inch breakout, no gland		
		В	33 inch breakout, with gland		
		С	33 inch breakout, with pulling grip		
		J	Propel, 23 inch breakout, with cable management clip, no pulling grip	ι	JOM
		к	Propel, 23 inch breakout, with cable management clip, with pulling grip	F	Feet
		1	33/60 inch breakout, no gland	М	Mete
		2	33/60 inch breakout, with gland on side A		
		3	33/60 inch breakout, with pulling grip and gland on side A		
		4	33/120 inch breakout, no gland		
		5	33/120 inch breakout, with gland on side A		
		6	33/120 inch breakout, with pulling grip and gland on side A		
		Т	33 inch breakout, with gland on side A		
		U	33 inch breakout, with pulling grip and gland on side A		
		V	60 inch breakout, no gland		
		w	60 inch breakout, with pulling grip		
		Ρ	120 inch breakout, no gland		
		Q	120 inch breakout, with pulling grip		

#### Mechanical Specifications

#### Cable Retention Strength, maximum

11.24 lb @ 0 ° | 4.40 lb @ 90 °

#### **Optical Specifications**

Fiber Mode	Multimode
Fiber Type	OM5, LazrSPEED®

#### **Environmental Specifications**

**Operating Temperature** 

-10 °C to +60 °C (+14 °F to +140 °F)

Page 2 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 20, 2025



## UGV2P2XBM

**Environmental Space** 

Indoor | Plenum

#### Regulatory Compliance/Certifications

#### Agency Classification

ISO 9001:2015

2015 Designed, manufactured and/or distributed under this quality management system

#### Included Products

760256589 P-144-MP-5G-F24LM/30T	_	Fiber indoor cable, LazrSPEED® Plenum MPO Trunk Cable, 144 fiber with 24-fiber, 3.0mm subunits, Gel-free, Multimode OM5, Feet jacket marking, Lime green jacket color
860662279	-	MPO24,FEMALE,OM5,LIME,3.0MM
860662280	-	MPO24,MALE,OM5,LIME,3.0MM

Page 3 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 20, 2025

