UGVMPMXAK

Base Product



Ultra Low Loss (ULL) OM5 MPO12 (Unpinned) to MPO12 (Pinned), Fiber Trunk Cable Assembly, 72-Fiber, Plenum

Product Classification

Regional Availability	Asia Australia/New Zealand China Europe India Latin America Middle East/Africa North America			
Portfolio	CommScope®			
Product Type	Fiber trunk cable assembly			
Product Brand	SYSTIMAX ULL			
Ordering Note	For additional jacket colors, please contact a CommScope Sales Representative For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration			
General Specifications				
Color, boot A	Black			
Color, connector A	Lime green			
Color, boot B	Black			
Color, connector B	Lime green			
Construction Type	Stranded			
Furcation Color	Lime green			
Interface, Connector A	MPO-12/UPC Female			
Interface, Connector B	MPO-12/UPC Male			
Jacket Color	Lime green			
Polarity	Method B Enhanced (ULL)			

Fibers per Subunit, quantity Total Fibers, quantity

Dimensions

Breakout Length	33 in
Cable Assembly Length Range (m)	3 – 999
Cable Assembly Length Range (ft)	10 - 999

Page 1 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 19, 2025

12

72



UGVMPMXAK

Ordering Tree

BASE CODE - N					<u> </u>
Jacket Color			Breakout Length / Option		ength
N	Lime green	A	33 inch breakout, no gland		
		В	33 inch breakout, with gland		
		С	33 inch breakout, with pulling grip		
		1	33/60 inch breakout, no gland		
2		2	33/60 inch breakout, with gland on side A	ų	NOM
		3	33/60 inch breakout, with pulling grip and gland on side A	F	Feet Meter
		4	33/120 inch breakout, no gland		
		5	33/120 inch breakout, with gland on side A		
		6	33/120 inch breakout, with pulling grip and gland on side A		
		Т	33 inch breakout, with gland on side A		
		U	33 inch breakout, with pulling grip and gland on side A		
		v	60 inch breakout, no gland		
		w	60 inch breakout, with pulling grip		
		Ρ	120 inch breakout, no gland		
		Q	120 inch breakout, with pulling grip		

Mechanical Specifications

Cable Retention Strength, maximum	11.24 lb @ 0 ° 4.40 lb @ 90 °			
Optical Specifications				
Fiber Mode	Multimode			
Fiber Type	OM5, LazrSPEED®			

Environmental Specifications

Operating Temperature

-10 °C to +60 °C (+14 °F to +140 °F)

Page 2 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 19, 2025



UGVMPMXAK

Environmental Space

Indoor | Plenum

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

Included Products

760223008 P-072-MP-5G-F12LM	-	Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, 72 fiber multi-unit with 12 fiber subunits, Multimode OM5, Gel-free, Feet jacket marking, Lime green jacket color
860617232	-	MP012, ULTRA LOW LOSS, FEMALE, OM5, LIME, 3mm
860617240	-	MP012, ULTRA LOW LOSS, MALE, OM5, LIME, 3mm

Page 3 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 19, 2025

