UGX2X2XBF

Base Product



Ultra Low Loss (ULL) OM4 MPO24 (Pinned) to MPO24 (Pinned), Fiber Trunk Cable Assembly, 24-Fiber, Plenum

Product Classification

Regional Availability	Asia Australia/New Zealand China Europe India Latin America Middle East/Africa North America	
Portfolio	CommScope®	
Product Type	Fiber trunk cable assembly	
Product Brand	SYSTIMAX ULL	
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration	

General Specifications

Cable Assembly Length Range (ft)

•	
Color, boot A	Red
Color, connector A	Aqua
Color, boot B	Red
Color, connector B	Aqua
Construction Type	Stranded
Furcation Color	Aqua
Interface, Connector A	MPO-24/UPC Male
Interface, Connector B	MPO-24/UPC Male
Jacket Color	Aqua
Polarity	Method B Enhanced (ULL)
Fibers per Subunit, quantity	24
Total Fibers, quantity	24
Dimensions	
Breakout Length	33 in
Cable Assembly Length Range (m)	3 - 999

Page 1 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 27, 2025

10 - 999



UGX2X2XBF

Ordering Tree

	E	ASE C	CODE - M . .	Ŀ	·
Jac	cket Color		Breakout Length / Option		ength
М	Aqua	А	33 inch breakout, no gland		
		В	33 inch breakout, with gland		
		С	33 inch breakout, with pulling grip		
		J	Propel, 23 inch breakout, with cable management clip, no pulling grip	l	ЛОМ
		к	Propel, 23 inch breakout, with cable management clip, with pulling grip	F	Feet
		1	33/60 inch breakout, no gland	Μ	Meter
		2	33/60 inch breakout, with gland on side A		
		3	33/60 inch breakout, with pulling grip and gland on side A		
		4	33/120 inch breakout, no gland		
		5	33/120 inch breakout, with gland on side A		
		6	33/120 inch breakout, with pulling grip and gland on side A		
		Т	33 inch breakout, with gland on side A		
		U	33 inch breakout, with pulling grip and gland on side A		
		V	60 inch breakout, no gland		
		w	60 inch breakout, with pulling grip		
		Р	120 inch breakout, no gland		
		Q	120 inch breakout, with pulling grip		

Mechanical Specifications

Cable Retention Strength, maximum

11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM4, LazrSPEED®

Environmental Specifications

Operating Temperature

Environmental Space

-10 °C to +60 °C (+14 °F to +140 °F)

Indoor | Plenum

Page 2 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 27, 2025



UGX2X2XBF

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Included Products

760245199 P-024-MP-5K-F30AQ	_	Fiber indoor cable, LazrSPEED® Plenum MPO Light Duty for Patchcords, 24 fiber, Multimode OM4, Feet jacket marking, Aqua jacket color
860662278	-	MP024,MALE,OM3/4,AQUA,3.0MM

Page 3 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 27, 2025

