UGXMXMXAH

Base Product



Ultra Low Loss (ULL) OM4 MPO12 (Pinned) to MPO12 (Pinned), Fiber Trunk Cable Assembly, 48-Fiber, Plenum

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

Product Type Fiber trunk cable assembly

Product Brand SYSTIMAX ULL

Ordering Note For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length

may vary based on cable configuration

General Specifications

Color, boot ABlackColor, connector AAquaColor, boot BBlackColor, connector BAquaConstruction TypeStrandedFurcation ColorAqua

 Interface, Connector A
 MPO-12/UPC Male

 Interface, Connector B
 MPO-12/UPC Male

Jacket Color Agua

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 12

Total Fibers, quantity 48

Dimensions

Breakout Length 33 in


Cable Assembly Length Range (m) 3 - 999

Cable Assembly Length Range (ft) 10 - 999

COMMSCOPE®

UGXMXMXAH

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 $^{\circ}$ | 4.40 lb @ 90 $^{\circ}$

Optical Specifications

Fiber Mode Multimode

Fiber Type OM4, LazrSPEED®

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \text{ (+14 }^{\circ}\text{F to } +140 \,^{\circ}\text{F)}$

Environmental Space Indoor | Plenum

COMMSCOPE®

UGXMXMXAH

Regulatory Compliance/Certifications

Agency Classification

ANATEL Compliant

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



Included Products

760045369 – Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, 48 fiber multi-unit with 12 fiber subunits, P-048-MP-5K-F12AQ Multimode OM4, Gel-free, Feet jacket marking, Aqua jacket color

860366228 - MPO12, ULTRA LOW LOSS, MALE, OM3/4, AQUA, 3mm