# **UJGMXUCRM**

#### **Base Product**



Ultra Low Loss (ULL) Singlemode, MPO12 Pinned to Unconnectorized, Fiber Trunk Cable Assembly, 144-Fiber, Rollable Ribbon Central Tube, Low Smoke Zero Halogen/Riser

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

**Product Type** Fiber trunk cable assembly

Product Brand SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

### General Specifications

Color, boot A Black
Color, connector A Green

**Construction Type** Rollable ribbon

Furcation Color Yellow

Interface, Connector A MPO-12/APC Male

Interface, Connector B Unterminated

Jacket Color Yellow

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 12

Total Fibers, quantity 144

#### **Dimensions**


Cable Assembly Length Range (m) 3 - 999

Cable Assembly Length Range (ft) 10 - 999

**COMMSCOPE®** 

# **UJGMXUCRM**

## Ordering Tree



### Mechanical Specifications

Cable Retention Strength, maximum  $11.24 \text{ lb} @ 0 \degree | 4.40 \text{ lb} @ 90 \degree$ 

**Optical Specifications** 

**Fiber Mode** Singlemode

**Fiber Type** G.657.A2, TeraSPEED®

## **Environmental Specifications**

**Operating Temperature**  $-10 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \text{ (+14 }^{\circ}\text{F to } +140 \,^{\circ}\text{F)}$ 

**Environmental Space** Dual Rated LSZH/Riser

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



# **UJGMXUCRM**

### Included Products

760238831 Z-144-MP-8G-F12BK/D Indoor/Outdoor Low Smoke Zero Halogen Riser MPO Trunk Cable, 144 fiber multi-unit with 12 fiber subunits

860638317

- MPO12, ULTRA LOW LOSS, MALE, Singlemode, GREEN, 3mm

