UJXMPMXAM

Ultra Low Loss (ULL) OM4 MPO12 (Unpinned) to MPO12 (Pinned), Fiber Trunk Cable Assembly, 144-Fiber, Low Smoke Zero Halogen (LSZH)

Product Classification

|	
Regional Availability	Asia	Australia/New Zealand	China	Europe	India	Latin America	Middle East/Africa	North America
Portfolio	CommScope®
Product Type	Fiber trunk cable assembly
Product Brand	SYSTIMAX ULL
Ordering Note	For additional jacket colors, please contact a CommScope Sales Representative	For lengths greater than 999 ft (304 m), orders must be in meters	Minimum length may vary based on cable configuration

General Specifications

Color, boot A	Black
Color, connector A	Aqua
Color, boot B	Black
Color, connector B	Aqua
Construction Type	Stranded
Furcation Color	Aqua
Interface, Connector A	MPO-12/UPC Female
Interface, Connector B	MPO-12/UPC Male
Jacket Color	Aqua
Polarity	Method B Enhanced (ULL)
Fibers per Subunit, quantity	12
Total Fibers, quantity	144

Dimensions

Breakout Length	33 in
Cable Assembly Length Range (m)	3 – 999
Cable Assembly Length Range (ft)	10 – 999

COMMSCOPE®

Ordering Tree

BASE CODE	-	M	.	.	.	.	.

Jacket Color

M	Aqua

Breakout Length / Option

A	33 inch breakout, no gland
B	33 inch breakout, with gland
C	33 inch breakout, with pulling grip
1	33/60 inch breakout, no gland
2	33/60 inch breakout, with gland on side A
3	33/60 inch breakout, with pulling grip and gland on side A
4	33/120 inch breakout, no gland
5	33/120 inch breakout, with gland on side A
6	33/120 inch breakout, with pulling grip and gland on side A
T	33 inch breakout, with gland on side A
U	33 inch breakout, with pulling grip and gland on side A
V	60 inch breakout, no gland
W	60 inch breakout, with pulling grip
P	120 inch breakout, no gland
Q	120 inch breakout, with pulling grip

Length

UOM

F	Feet
M	Meter

Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode Multimode

Fiber Type OM4, LazrSPEED®

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

COMMSCOPE®

UJXMPMXAM

Environmental Space   Dual Rated LSZH/Riser | Indoor

Regulatory Compliance/Certifications

Agency	Classification
ANATEL	Compliant
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

Included Products

760067520 N-144-MP-5K-F12AQ/D	–	Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk, 144 fiber multi-unit with 12 fiber subunits, Gel-free, Multimode OM4, Feet jacket marking, Aqua jacket color, Dca flame rating
860366210	–	MPO12, ULTRA LOW LOSS, FEMALE, OM3/4, AQUA, 3mm
860366228	–	MPO12, ULTRA LOW LOSS, MALE, OM3/4, AQUA, 3mm

COMMSCOPE®