## UJXMXMXAD

#### **Base Product**



Ultra Low Loss (ULL) OM4 MPO12 (Pinned) to MPO12 (Pinned), Fiber Trunk Cable Assembly, 12-Fiber, Low Smoke Zero Halogen (LSZH)

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

**Product Type** Fiber trunk cable assembly

Product Brand SYSTIMAX ULL

Ordering Note Not available in the United States or Canada

#### General Specifications

Color, boot ABlackColor, connector AAquaColor, boot BBlackColor, connector BAquaConstruction TypeStranded

Furcation Color Aqua

 Interface, Connector A
 MPO-12/UPC Male

 Interface, Connector B
 MPO-12/UPC Male

Jacket Color Aqua

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 12

Total Fibers, quantity 12

#### **Dimensions**

Breakout Length 33 in


Cable Assembly Length Range (m) 3 - 999

Cable Assembly Length Range (ft) 10 - 999



## **UJXMXMXAD**

### Ordering Tree



### Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode Multimode

**Fiber Type** OM4, LazrSPEED®

## **Environmental Specifications**

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Dual Rated LSZH/Riser | Indoor

Page 2 of 3



# **UJXMXMXAD**

### Regulatory Compliance/Certifications

Agency Classification

ANATEL Compliant

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



#### Included Products

760067470 – Fiber Indoor Cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk Cable, 12 fiber, N-012-MP-5K-F12AQ/D Gel-free, Multimode OM4, Dca Flame Rating, Feet jacket marking, Aqua jacket color

860366228 - MPO12, ULTRA LOW LOSS, MALE, OM3/4, AQUA, 3mm