## UKGMPMPDH

#### **Base Product**



Ultra Low Loss (ULL) Singlemode, MPO12 Unpinned to MPO12 Unpinned, Fiber Trunk Cable Assembly, 48-Fiber, Indoor/Outdoor Armored, Low Smoke Zero Halogen/Riser

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | China | India | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

Product Type Fiber trunk cable assembly

Product Brand SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

### General Specifications

Color, boot ABlackColor, connector AGreenColor, boot BBlackColor, connector BGreen

Construction Type Armored | Stranded

Furcation Color Yellow

 Interface, Connector A
 MPO-12/APC Female

 Interface, Connector B
 MPO-12/APC Female

Jacket Color Black

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 12

Total Fibers, quantity 48

#### **Dimensions**

Breakout Length 33 in

Cable Assembly Length Range (m) 3 - 999


Cable Assembly Length Range (ft) 10 - 999

Page 1 of 3



## UKGMPMPDH

### Ordering Tree



### Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

**Optical Specifications** 

**Fiber Mode** Singlemode

**Fiber Type** G.657.A2, TeraSPEED®

## **Environmental Specifications**

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Dual Rated LSZH/Riser | Indoor/Outdoor

## Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



#### Included Products

760238843 Z-048-MZ-8G-F12BK Fiber Indoor/Outdoor cable, Low Smoke Zero Halogen Riser MPO Trunk, interlocking aluminum armored, 48 fiber multi-unit with 12 fiber subunits, Singlemode G.657.A2, Feet jacket marking, Black jacket color

Page 2 of 3

# UKGMPMPDH

860638318

- MPO12, ULTRA LOW LOSS, FEMALE, Singlemode, GREEN, 3mm

