
ULGLCLCCL

Base Product



Ultra Low Loss ULL TeraSPEED® LC/UPC to LC/UPC Ruggedized fanout Cable, 96-Fiber, Plenum

Product Classification

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

Product Type Ruggedized fanout

Product Brand SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may vary

based on cable configuration

General Specifications

Color, boot A Blue

Color, connector A Green

Color, boot B Blue

Color, connector B Blue

Construction Type Stranded

Furcation Color Yellow

Interface, Connector A LC/UPC

Interface Feature, connector A ULL

Interface, Connector B LC/UPC

Interface Feature, connector B ULL

Jacket Color Yellow

Fibers per Subunit, quantity 12

Total Fibers, quantity 96

Dimensions

Cable Assembly Length Range (m) 3 - 999



ULGLCLCCL

8 - 999Cable Assembly Length Range (ft)

Optical Specifications

Fiber Mode Singlemode

G.657.A2, TeraSPEED® **Fiber Type**

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Indoor | Plenum

Regulatory Compliance/Certifications

Classification Agency **ANATEL** Compliant

CHINA-ROHS Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system ISO 9001:2015 REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant **UK-ROHS** Compliant





Included Products

Fiber Indoor Cable, Plenum MPO Trunk, 96 fiber multi-unit with 12 fiber subunits, Singlemode G. 760249010 P-096-MP-8G1-F12YL/20T 657.A2/B2, Gel-free, Feet jacket marking, Yellow jacket color, Light Duty

