## ULGSASACD

**Base Product** 



# Ultra Low Loss ULL TeraSPEED® SC/APC to SC/APC Ruggedized fanout Cable, 12-Fiber, Plenum, 12 fiber PmP 2.0 mm Dca

in meters | Minimum length may vary based on cable configuration

#### Product Classification

Regional Availability	Asia   Australia/New Zealand   Europe   Latin America   Middle East/Africa   North America
Portfolio	CommScope®
Product Type	Ruggedized fanout
Product Brand	SYSTIMAX ULL
Ordering Note	For additional jacket colors, please contact a CommScope Sales Representative   For lengths greater than 999 ft (304 m), orders must be

#### General Specifications

Color, boot A	Green
Color, connector A	Green
Color, boot B	Green
Color, connector B	Green
Construction Type	Stranded
Furcation Color	Yellow
Interface, Connector A	SC/APC
Interface Feature, connector A	ULL
Interface, Connector B	SC/APC
Interface Feature, connector B	ULL
Jacket Color	Yellow
Fibers per Subunit, quantity	12
Total Fibers, quantity	12
Dimensions	
Cable Assembly Length Range (m)	3 - 999

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: November 18, 2024



## ULGSASACD

Cable Assembly Length F	Range (ft)	8 - 999	
Optical Specifications			
Fiber Mode		Singlemode	
Fiber Type		G.657.A2, TeraSPEED®	
Environmental Specifications			
Operating Temperature		-10 °C to +60 °C (+14 °F to +140 °F)	
EN50575 CPR Cable EuroClass Fire Performance		Dca	
Environmental Space		Indoor   Plenum	
Regulatory Compliance/Certifications			
Agency	Classification		
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system		
Included Products			

760242049 P-012-MP-8G-F12YL/20T Fiber indoor cable, Plenum for MPO Trunks, 12 fiber, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color

Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: November 18, 2024

