ULGSASACK

Base Product



Ultra Low Loss ULL TeraSPEED® SC/APC to SC/APC Ruggedized fanout Cable, 72-Fiber, Plenum, 12 fiber PmP 2.0 mm Dca

Product Classification

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle

East/Africa | North America

Portfolio CommScope®

Product Type Ruggedized fanout

Product Brand SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales

Representative | For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may vary based on cable configuration

General Specifications

Color, boot A Green

Color, connector A Green

Color, boot B Green

Color, connector B Green

Construction Type Stranded

Furcation Color Yellow

Interface, Connector A SC/APC

Interface Feature, connector A ULL

Interface, Connector B SC/APC

Interface Feature, connector B ULL

Jacket Color Yellow

Fibers per Subunit, quantity 12

Total Fibers, quantity 72

Dimensions

Cable Assembly Length Range (m) 3 - 999
Cable Assembly Length Range (ft) 8 - 999

Page 1 of 2



ULGSASACK

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A2, TeraSPEED®

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

EN50575 CPR Cable EuroClass Fire Performance

Environmental Space Indoor | Plenum

Regulatory Compliance/Certifications

Classification **Agency**

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Included Products

Fiber indoor cable, Plenum MPO Trunk, 72 fiber multi-unit with 12 fiber subunits, Singlemode G. 760242057 P-072-MP-8G-F12YL/20T

657.A2/B2, Feet jacket marking, Yellow jacket color

