ULVLCLCCG

Base Product



Ultra Low Loss ULL LazrSPEED® 550 OM5 LC/UPC to LC/UPC Ruggedized fanout Cable, 36-Fiber, Plenum, 12 fiber PmP 2.0 mm Dca

in meters | Minimum length may vary based on cable configuration

Product Classification

Regional Availability	Asia Australia/New Zealand Europe Latin America Middle East/Africa North America	
Portfolio	CommScope®	
Product Type	Ruggedized fanout	
Product Brand	SYSTIMAX ULL	
Ordering Note	For additional jacket colors, please contact a CommScope Sales Representative For lengths greater than 999 ft (304 m), orders must be	

General Specifications

Color, boot A	Blue
Color, connector A	Black
Color, boot B	Blue
Color, connector B	Black
Construction Type	Stranded
Furcation Color	Lime green
Interface, Connector A	LC/UPC
Interface, Connector B	LC/UPC
Interface Feature, connector B	ULL
Jacket Color	Lime green
Fibers per Subunit, quantity	12
Total Fibers, quantity	36
Dimensions	
Cable Assembly Length Range (m)	3 - 305

Cable Assembly Length Range (ft)	10 - 999

Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 12, 2024



ULVLCLCCG

Ordering Tree

	BASE CODE - N				
Jacket Color E			Breakout Length / Option	Length	
N	Lime green	E 24 inch breakout, no gland			
		F	24 inch breakout, with gland		
		1	33/60 inch breakout, no gland		
		2	33/60 inch breakout, with gland		
		3	33/60 inch breakout, with pulling grip		JOM
		н	48 inch breakout, no gland	F	Feet
		J	48 inch breakout, with gland	М	Meter
		L	72 inch breakout, no gland		
		М	72 inch breakout, with gland		
		S	36 inch breakout, no gland		
		U	36 inch breakout, with gland		
		v	60 inch breakout, no gland		
		W	60 inch breakout, with pulling grip		

Optical Specifications

Fiber Mode

Fiber Type

Multimode OM5, LazrSPEED®

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
EN50575 CPR Cable EuroClass Fire Performance	Dca
Environmental Space	Indoor Plenum

Regulatory Compliance/Certifications

Agency	Classification
ANATEL	Compliant
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 12, 2024



ULVLCLCCG

REACH-SVHC

ROHS UK-ROHS Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant Compliant



Included Products

760242117 P-036-MP-5G-F12LM/20T Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, 36 fiber multi-unit with 12 fiber subunits, Multimode OM5, Gel-free, Feet jacket marking, Lime green jacket color

Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 12, 2024

