AGX2P2PBK

Base Product



OM4 MPO24 (Unpinned) to MPO24 (Unpinned), Fiber Trunk Cable Assembly, 72-Fiber, Method A, Plenum

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

Product Type Fiber trunk cable assembly

Ordering Note For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length

may vary based on cable configuration

General Specifications

Color, boot ARedColor, connector AAquaColor, boot BRedColor, connector BAquaConstruction TypeStrandedFurcation ColorAqua

 Interface, Connector A
 MPO-24/UPC Female

 Interface, Connector B
 MPO-24/UPC Female

Jacket Color Aqua

Polarity Method A

Fibers per Subunit, quantity 24

Total Fibers, quantity 72

Dimensions


Cable Assembly Length Range (m) 3 - 999

Cable Assembly Length Range (ft) 10 - 999

Ordering Tree



AGX2P2PBK



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 $^{\circ}$ | 4.40 lb @ 90 $^{\circ}$

Optical Specifications

Fiber Mode Multimode

Fiber Type OM4, LazrSPEED®

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Environmental Space Indoor | Plenum

Regulatory Compliance/Certifications

COMMSCOPE®

AGX2P2PBK

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



Included Products

760256580 – Fiber indoor cable, LazrSPEED® Plenum MPO Trunk Cable, 72 fiber with 24-fiber, 3.0mm P-072-MP-5K-F24AQ/30T subunits, Gel-free, Multimode OM4, Feet jacket marking, Aqua jacket color

860662277 – MPO24,FEMALE,OM3/4,AQUA,3.0MM

