UQV2X2XHF

Base Product



Ultra Low Loss (ULL) OM5, MPO24 (Pinned) to MPO24 (Pinned), 24-Fiber, Plenum Patchcord

Product Classification

Regional Availability

Australia/New Zealand | Europe | Latin America | Middle East/Africa | North

America

Portfolio CommScope®

Product Type Fiber array cable assembly

Product Brand SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

General Specifications

Color, boot A Red

Color, connector A Lime green

Color, boot B Red

Color, connector BLime greenConstruction TypeStrandedFurcation ColorLime green

 Interface, Connector A
 MPO-24/UPC Male

 Interface, Connector B
 MPO-24/UPC Male

Jacket Color Lime green

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 24

Total Fibers, quantity 24

Dimensions


Cable Assembly Length Range (m) 3 - 999

Cable Assembly Length Range (ft) 10 - 999

COMMSCOPE®

UQV2X2XHF

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode Multimode

Fiber Type OM5, LazrSPEED®

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Indoor | Plenum

Regulatory Compliance/Certifications

Classification **Agency**

Designed, manufactured and/or distributed under this quality management system ISO 9001:2015

Included Products

Fiber indoor cable, LazrSPEED® Plenum MPO Light Duty for Patchcords, 24 fiber, Multimode 760245200 P-024-MP-5G-F30LM

OM5, Feet jacket marking, Lime green jacket color

MPO24,MALE,OM5,LIME,3.0MM 860662280