UQX2XQPHF

Base Product



Ultra Low Loss OM4, MPO24 (Pinned) to MPO8 QSFP (Unpinned), Fiber Extension Cable Assembly, 24-Fiber, Plenum

Product Classification

Regional Availability Australia/New Zealand | Europe | Latin America | Middle East/Africa | North

America

Portfolio CommScope®

Product Type Fiber array cable assembly

Product Brand SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

General Specifications

Color, boot A Red

Color, connector A Aqua

Color, boot B Gray

Color, connector B Aqua

Construction Type Stranded

Furcation Color Aqua

Interface, Connector A MPO-24/UPC Male

Interface, Connector B MPO-08/UPC Female

Interface Feature, connector B QSFP configuration

Jacket Color Aqua

Polarity Method B Enhanced (ULL)

Total Fibers, quantity 24

Dimensions


COMMSCOPE®

UQX2XQPHF

Cable Assembly Length Range (m) 3 - 999

Cable Assembly Length Range (ft) 10 - 999

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode Multimode

Fiber Type OM4, LazrSPEED®

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Indoor | Plenum

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Included Products

760245199 – Fiber indoor cable, LazrSPEED® Plenum MPO Light Duty for Patchcords, 24 fiber, Multimode P-024-MP-5K-F30AQ OM4, Feet jacket marking, Aqua jacket color

860633307 – MPO8, ULTRA LOW LOSS, FEMALE, OM3/4, AQUA, 3mm

Page 2 of 3



UQX2XQPHF

860662278

MPO24,MALE,OM3/4,AQUA,3.0MM

