UQXQPMPHF

Base Product



Ultra Low Loss OM4, MPO8 QSFP (Unpinned) to MPO12 (Unpinned), Fiber Extension Cable Assembly, 24-Fiber, Plenum

Product Classification

Regional Availability Australia/New Zealand | Europe | Latin America | Middle East/Africa | North

America

Portfolio CommScope®

Product Type Fiber array cable assembly

Product Brand SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

General Specifications

Color, boot A Gray

Color, connector A Aqua

Color, boot B Black

Color, connector B Aqua

Construction Type Stranded

Furcation Color Aqua

Interface, Connector A MPO-08/UPC Female

Interface Feature, connector A QSFP configuration

Interface, Connector B MPO-12/UPC Female

Jacket Color Aqua

Polarity Method B Enhanced (ULL)

Total Fibers, quantity 24


Dimensions

Cable Assembly Length Range (m) 1 - 305

Cable Assembly Length Range (ft) 1 - 999

UQXQPMPHF

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum $11.24 \text{ lb} @ 0 \degree + 4.40 \text{ lb} @ 90 \degree$

Optical Specifications

Fiber Mode Multimode

Fiber Type OM4, LazrSPEED®

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Indoor | Plenum

Regulatory Compliance/Certifications

Agency Classification
ANATEL Compliant

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



Included Products

760245199 P-024-MP-5K-F30AQ Fiber indoor cable, LazrSPEED® Plenum MPO Light Duty for Patchcords, 24 fiber, Multimode OM4, Feet jacket marking, Aqua jacket color

Page 2 of 3

UQXQPMPHF

860366210 – MPO12, ULTRA LOW LOSS, FEMALE, OM3/4, AQUA, 3mm

860633307 – MPO8, ULTRA LOW LOSS, FEMALE, OM3/4, AQUA, 3mm

