URX2X2XHF

Base Product



Ultra Low Loss (ULL) OM4 MPO/24 (Pinned) to MPO/24 (Pinned), 24-Fiber, Low Smoke Zero Halogen (LSZH)/Riser

Product Classification

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

Product Type Fiber array cable assembly

Product Brand SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

General Specifications

Color, boot ARedColor, connector AAquaColor, boot BRedColor, connector BAquaConstruction TypeStranded

Furcation Color Aqua

 Interface, Connector A
 MPO-24/UPC Male

 Interface, Connector B
 MPO-24/UPC Male

Jacket Color Aqua

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 24

Total Fibers, quantity 24


Dimensions

Cable Assembly Length Range (m)1-305Cable Assembly Length Range (ft)1-999

COMMSC PE®

URX2X2XHF

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0° | 4.40 lb @ 90°

Optical Specifications

Fiber Mode Multimode

Fiber Type OM4, LazrSPEED®

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Indoor | Low Smoke Zero Halogen (LSZH)

Regulatory Compliance/Certifications

Classification **Agency**

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Included Products

Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser Light Duty for MPO 760256685 N-024-MP-5K-F30AQ/D

Patchcords, 24 fiber, Multimode OM4, Gel-free, Feet jacket marking, Aqua jacket color, Dca

flame rating

MPO24,MALE,OM3/4,AQUA,3.0MM 860662278

