AQXMPMPGD

Base Product



OM4 MPO12 (Unpinned) to MPO12 (Unpinned), Fiber Patch Cord, 12-Fiber, Method A, Plenum

Product Classification

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

Product Type Fiber array cable assembly

Ordering Note For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length

may vary based on cable configuration

General Specifications

Color, boot ABlackColor, connector AAquaColor, boot BBlackColor, connector BAquaConstruction TypeStranded

Furcation Color Aqua

 Interface, Connector A
 MPO-12/UPC Female

 Interface, Connector B
 MPO-12/UPC Female

Jacket Color Aqua

Polarity Method A

Fibers per Subunit, quantity 12

Total Fibers, quantity 12

Dimensions


Cable Assembly Length Range (m) 1 - 305

Cable Assembly Length Range (ft) 1 - 999

Ordering Tree



AQXMPMPGD



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 $^{\circ}$ | 4.40 lb @ 90 $^{\circ}$

Optical Specifications

Fiber Mode Multimode

Fiber Type OM4, LazrSPEED®

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C to } +60 \,^{\circ}\text{C (+14 °F to } +140 \,^{\circ}\text{F)}$

Environmental Space Indoor | Plenum

Regulatory Compliance/Certifications

Agency	Classification
ANATEL	Compliant
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



Included Products

760074997 – Fiber indoor cable, LazrSPEED® Plenum MPO Light Duty for Patchcords, 12 fiber, Multimode

P-012-MP-5K-F30AQ OM4, Feet jacket marking, Aqua jacket color

860366210 - MPO12, ULTRA LOW LOSS, FEMALE, OM3/4, AQUA, 3mm

COMMSCOPE®