

Fiber Optic Patch Cord, OM3, LC to LC duplex, 1.8 mm LSZH & OFNR, 3 m, aqua

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | India

Portfolio CommScope®

Product Type Fiber patch cord, duplex

Product Series 210

General Specifications

Connector A, quantity 2

Color, boot ABeigeColor, connector ABeige

Color, boot BBeigeColor, connector BBeige

Interface, Connector A LC/UPC
Interface, Connector B LC/UPC

Jacket Color Aqua

Polarity Pairs, flipped

Total Fibers, quantity 2

Dimensions


Connector B, quantity

Cord Length 3 m | 9.843 ft

Diameter Over Jacket 1.8 mm | 0.071 in

Ordering Tree





Optical Specifications

Fiber Mode Multimode

Fiber Type OM3, LazrSPEED®

Insertion Loss, maximum, connector A0.3 dBInsertion Loss, maximum, connector B0.3 dBReturn Loss, minimum, connector A20 dBReturn Loss, minimum, connector B20 dB

Environmental Specifications

Environmental SpaceDual Rated LSZH/Riser

Qualification Standards IEC 60332-1 | IEC 60332-3 | IEC 60754 | IEC 61034

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



2105027-3



