



Copper Patch Cord, RJ45 to 4P AMP-TWIST plug, cat 6A, S/FTP, stranded, LSZH, white, 2 m

**OBSOLETE**

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA
<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Twisted pair patch cord

## General Specifications

<b>ANSI/TIA Category</b>	6A
<b>Cable Type</b>	S/FTP (shielded)
<b>Interface, Connector A</b>	RJ45 plug
<b>Interface, Connector B</b>	4P AMP-TWIST Plug
<b>Jacket Color</b>	White
<b>Pairs, quantity</b>	4

## Dimensions

<b>Cord Length</b>	2 m   6.562 ft
<b>Diameter Over Jacket</b>	5.9 mm   0.232 in

## Environmental Specifications

<b>Operating Temperature</b>	-20 °C to +60 °C (-4 °F to +140 °F)
<b>Environmental Space</b>	Low Smoke Zero Halogen (LSZH)

## Regulatory Compliance/Certifications

# 336488-2

---

**Agency**

CHINA-ROHS  
RCM  
REACH-SVHC  
ROHS

**Classification**

Below maximum concentration value  
Compliant to electrical safety & telecommunications requirements  
Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)  
Compliant

