



Copper Patch Cord, RJ45 to 4P AMP-TWIST plug, cat 6A, S/FTP, stranded, LSZH, white, 3 m

OBSOLETE

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA
Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord

General Specifications

ANSI/TIA Category	6A
Cable Type	S/FTP (shielded)
Interface, Connector A	RJ45 plug
Interface, Connector B	4P AMP-TWIST Plug
Jacket Color	White
Pairs, quantity	4

Dimensions

Cord Length	3 m 9.843 ft
Diameter Over Jacket	5.9 mm 0.232 in

Environmental Specifications

Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Environmental Space	Low Smoke Zero Halogen (LSZH)

Regulatory Compliance/Certifications

336488-3

Agency

CHINA-ROHS

RCM

REACH-SVHC

ROHS

**Classification**

Below maximum concentration value

Compliant to electrical safety & telecommunications requirements

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant