



RJ45 Patch Cord, category 6A, XG, SL, shielded F/UTP, PVC, white, 10 ft

**OBSOLETE**

This product was discontinued on: May 1, 2018

**Replaced By:**

NPC6ASVDB

NPC RJ45 Patch Cord, category 6A, Shielded, CM (PVC)

Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA
Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord

General Specifications

ANSI/TIA Category	6A
Cable Type	F/UTP (shielded)
Conductor Type	Stranded
Interface, Connector A	RJ45 plug
Interface, Connector B	RJ45 plug
Jacket Color	White
Pairs, quantity	4
Wiring	T568B

Dimensions

Cord Length	3.05 m   10.007 ft
Diameter Over Jacket	6 mm   0.236 in
Compatible Conductor Gauge, stranded	26 AWG

# 1-1933885-0

## Material Specifications

**Conductor Material** Tin plated copper

## Environmental Specifications

**Operating Temperature** -20 °C to +60 °C (-4 °F to +140 °F)

**Storage Temperature** -20 °C to +80 °C (-4 °F to +176 °F)

**Environmental Space** Non-plenum

**Flammability Rating** CM

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

