



RJ45 Patch Cord, category 6, S/FTP, LZSH, stranded, black, 3 m

**OBSOLETE**

This product was discontinued on: May 1, 2018

**Replaced By:**

NPC06SZDB                      NPC RJ45 Patch Cord, category 6, Shielded, LSZH

Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA
Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord

General Specifications

ANSI/TIA Category	6
Cable Type	S/FTP (shielded)
Conductor Type	Stranded
Interface, Connector A	RJ45 plug
Interface, Connector B	RJ45 plug
Jacket Color	Black
Pairs, quantity	4

Dimensions

Cord Length	3 m   9.843 ft
Diameter Over Jacket	5.59 mm   0.22 in
Compatible Conductor Gauge, stranded	26 AWG

Environmental Specifications

Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Environmental Space	Low Smoke Zero Halogen (LSZH)

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

