



RJ45 Patch Cord, category 6, trans SL boot, violet, 7 ft

**OBSOLETE**  
This product was discontinued on: May 1, 2018

Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA
Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord

General Specifications

ANSI/TIA Category	6
Cable Type	U/UTP (unshielded)
Interface, Connector A	RJ45 plug
Interface, Connector B	RJ45 plug
Jacket Color	Violet
Pairs, quantity	4
Wiring	T568B

Dimensions

Cord Length	2.13 m   6.988 ft
Compatible Conductor Gauge, stranded	24 AWG

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Environmental Space	Non-plenum
Flammability Rating	CM

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

