

2-2111375-5 | TMRJ-1SUPB-SH025M



MRJ21™ High Speed Cable Assembly, 180° MRJ21 to Plug, 1GbE, 24-pair, CMR, 25 m, blue

- Universal modular copper cabling platform for applications such as Gigabit Ethernet, VoIP and Power over Ethernet
- Increased I/O port density and cleaner cabling schemes compared to RJ45 connectors and cabling
- Robust die cast cable covers provide straight, or 45 deg left/right cable exit for ease of routing

OBSOLETE

This product was discontinued on: June 1, 2022

Product Classification

| | |
|-----------------------|-------------------------------|
| Regional Availability | Latin America North America |
| Portfolio | CommScope® |
| Product Type | Copper trunk cable assembly |
| Product Brand | MRJ21™ |
| Product Series | MRJ21 |

General Specifications

| | |
|--------------------------------|------------------|
| ANSI/TIA Category | 6 |
| Application | Ethernet, 1 GbE |
| Cable Type | F/UTP (shielded) |
| Conductor Type | Solid |
| Construction Type | Stranded |
| Interface, Connector A | MRJ21 plug |
| Interface Feature, connector A | Backshell, 180° |
| Interface, Connector B | RJ45 plug |
| Interface Feature, connector B | Booted |
| Jacket Color | Blue |
| Pairs, quantity | 24 |
| Total Ports, quantity | 6 |

2-2111375-5 | TMRJ-1SUPB-SH025M

Dimensions

| | |
|--|--------------------|
| Cord Length | 25 m 82.021 ft |
| Diameter Over Jacket | 11.7 mm 0.461 in |
| Compatible Conductor Gauge, solid | 24 AWG |

Electrical Specifications

| | |
|------------------------------|-------|
| Safety Voltage Rating | 150 V |
|------------------------------|-------|

Material Specifications

| | |
|---------------------------|-------------|
| Conductor Material | Bare copper |
|---------------------------|-------------|

Environmental Specifications

| | |
|----------------------------|--------|
| Environmental Space | Plenum |
| Flammability Rating | CM |
| Safety Standard | cUL |

Packaging and Weights

| | |
|---------------------------|---|
| Packaging quantity | 1 |
|---------------------------|---|

Regulatory Compliance/Certifications

| Agency | Classification |
|------------|---|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

