



Fiber Optic Patch Cord, Multi-fiber, Singlemode, 24 fibers, SC/UPC to SC /UPC, yellow, 20 m

Product Classification

Regional Availability	Latin America North America
Product Type	Fiber distribution cable assembly
Product Series	FPM

General Specifications

Connector A, quantity	24
Color, boot A	Blue
Color, connector A	Blue
Connector B, quantity	24
Color, boot B	Blue
Color, connector B	Blue
Construction Type	Stranded
Interface, Connector A	SC/UPC
Interface, Connector B	SC/UPC
Jacket Color	Yellow
Total Fibers, quantity	24

Dimensions

Breakout Length, connector A	635 mm 25 in
Breakout Length, connector B	635 mm 25 in
Cord Length	20 m 65.617 ft

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	OS2
Insertion Loss, maximum, connector A	0.2 dB

Insertion Loss, maximum, connector B	0.2 dB
Return Loss, minimum, connector A	57 dB
Return Loss, minimum, connector B	57 dB

Environmental Specifications

Environmental Space	Plenum
----------------------------	--------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

